

Prusa3D Prusament Viva La Bronze PLA Silk Bronze

Material Engineering Report
MaterialID MAT0081

3DPiceland Engineering Platform
3DPiceland Labs
Generated with 3DPiceland Engineering Platform v60.0.6
WORKFLOW-RELIABILITY - Bug Fixes and Workflow
Reliability
Generated 2026-08-25 19:02:26

Public-data contract: This static report contains only allowlisted material identity, public links, canonical MSRP and existing Verified Material Summary / governed score outputs. It excludes raw specimen rows and non-public operational data.

TEST COVERAGE

Complete

ENGINEERING AXES

6/6

PUBLIC MSRP

\$30.40 USD/kg

Material identity

MaterialID	MAT0081
Material	Prusa3D Prusament Viva La Bronze PLA Silk Bronze
Manufacturer	Prusa3D
Product line	Prusament
Base material	PLA
Category	Standard
Variant / finish	Silk
Reinforcement	—
Color	Bronze

Governed engineering profile

Overall


45/100

Tensile	35/100
Impact	15/100
Stiffness	64/100
Consistency	86/100
Layer adhesion	24/100
Thermal	27/100
Best available axis	consistency

Engineering score profile



Engineering radar



Fixture thermal result

54 °C · score 27/100 · method 3dp-thermal-deflection-fixture-v1

Nearby BlueDOT probe-indicated fixture temperature from a non-standard comparative 3DPlceland method; not ASTM D648, ISO 75, specimen temperature, certified HDT or a manufacturer limit.

Material and manufacturer context

Metric	Selected material	Material average	Manufacturer average
Overall	45/100	50/100	49/100
Tensile	35/100	29/100	31/100
Impact	15/100	24/100	21/100
Stiffness	64/100	87/100	84/100
Consistency	86/100	79/100	79/100
Layer adhesion	24/100	30/100	32/100
Thermal	27/100	—	—

Verified measurement results

Existing Verified Material Summary outputs. The public renderer does not read raw specimen rows or recalculate these values.

Measurement	Average	Std. deviation	CV	Samples	Confidence
Tensile upright	10.715 MPa	2.098 MPa	19.6%	9	9/10
Tensile flat	45.05 MPa	5.158 MPa	11.4%	10	10/10
Impact upright	76.218 kJ/m ²	11.58 kJ/m ²	15.2%	10	10/10
Impact flat	215.37 kJ/m ²	20.33 kJ/m ²	9.4%	10	10/10
Stiffness modulus	1922.002 MPa	—	—	—	—
Stiffness deflection	2.823 mm	—	—	—	—

Measurement provenance

Canonical per-module measured dates from SQLite, shown in unambiguous ISO format. Missing dates are not inferred.

Module	Measured date
Tensile	Not recorded
Impact	Not recorded
Stiffness	Not recorded
Thermal	Not recorded

Engineering interpretation

Summary: Prusa3D Prusament Viva La Bronze PLA Silk Bronze has a specialized or limited engineering profile. It is below its material-family average by 5,5 points and below its manufacturer average by 4,8 points. Its strongest measured axis is Consistency, while the weakest axis is Impact.

Data-driven review: Prusa3D Prusament Viva La Bronze PLA Silk Bronze is best understood as a repeatable material for cosmetic, concept and low-load prototype work. Compared with the current verified dataset, it ranks better than 37% overall, is below the material-family average by 5,5 points, and is below the manufacturer average by 4,8 points. Its strongest engineering signal is Consistency, while Impact is the main limitation to consider before using it for demanding applications.

BEST FEATURE

Consistency

MAIN LIMITATION

Impact

DATASET POSITION

Better than 37%
148 / 234

Strengths

- Consistency: 86/100. Repeatability is one of the stronger signals in this material profile.
- Tensile: 35/100. Tensile behavior is competitive against the material-family context.

Limitations

- Tensile: 35/100. Avoid using this as the primary choice for tensile-loaded parts.
- Impact: 15/100. Avoid high impact or shock-loaded components without additional validation.
- Stiffness: 64/100. Expect less shape stability than the stronger materials in the same family.
- Layer adhesion: 24/100. Z-axis performance should be treated with caution.

Engineering trade-offs

- Good repeatability does not compensate for low tensile capability in load-bearing designs.
- The report should be read as a suitability warning rather than a general-purpose recommendation.

Recommended applications

- Repeatable print jobs and production-style batches
- Cosmetic parts, concept models or low-load prototypes
- Avoid high tensile load applications
- Avoid high impact components

Metric rankings and percentiles

Metric	Score	Rank	Percentile
Overall	45/100	148 / 234	Better than 37%
Tensile	35/100	47 / 226	Better than 80%
Impact	15/100	184 / 226	Better than 19%
Stiffness	64/100	173 / 223	Better than 23%
Consistency	86/100	18 / 231	Better than 93%
Layer adhesion	24/100	112 / 226	Better than 51%
Thermal	27/100	119 / 209	Better than 44%

Decision guidance

- Use this material mainly for low-load, visual or experimental parts.
- Review the listed alternatives if the application needs stronger overall performance.
- Do not choose it as a tensile-strength benchmark material.
- Avoid selecting it for impact-focused testing or shock-loaded designs.

Better alternatives

MaterialID	Material	Manufacturer	Overall	Tensile	Impact
MAT0069	ProtoPasta HTPLA Blood of My Enemies PLA Red	ProtoPasta	100/100	—	—
MAT0079	Polymaker PolyLight PLA Pro Black	Polymaker	65/100	35/100	52/100
MAT0109	Polymaker PolyMax PLA Black	Polymaker	64/100	32/100	62/100

Peer context

Highest-scoring same-base-material peers from the current governed dataset. This context is descriptive and is not recalculated by the public renderer.

MaterialID	Material	Manufacturer	Overall	Tensile	Impact
MAT0069	ProtoPasta HTPLA Blood of My Enemies PLA Red	ProtoPasta	100/100	—	—

MaterialID	Material	Manufacturer	Overall	Tensile	Impact
MAT0079	Polymaker PolyLight PLA Pro Black	Polymaker	65/100	35/100	52/100
MAT0109	Polymaker PolyMax PLA Black	Polymaker	64/100	32/100	62/100
MAT0080	Polymaker PolySonic PLA Pro Blue	Polymaker	64/100	30/100	58/100
MAT0076	BambuLab Tough+ PLA Tough+ Black	BambuLab	63/100	26/100	59/100
MAT0108	Polymaker PolyLight PLA Black	Polymaker	61/100	33/100	14/100
MAT0074	Winkle Matte PLA Matte Red	Winkle	60/100	34/100	—
MAT0122	Add:North Enhanced PLA Clear	Add:North	59/100	40/100	10/100

Public links

[Manufacturer website](#) [Video review](#) [Download PDF](#)

Methodology and limitations

Results are comparative 3DPlceland measurements from home-built test equipment. Thermal is a nearby BlueDOT probe-indicated fixture temperature, not ASTM D648, ISO 75 or specimen temperature. Missing evidence remains n/a. Scores and test results are not recalculated by this publishing layer and do not replace certified manufacturer datasheets or accredited laboratory testing.

- [Testing methodology](#).
- [Engineering methodology whitepaper](#)