

Sunlu Standard Blue PLA High Speed Blue

MaterialID MAT0182



3DPiceland Labs
Generated with 3DPiceland Engineering Platform v60.0.6
WORKFLOW-RELIABILITY - Bug Fixes and Workflow
Reliability
2026-08-25 19:04:35

Traceability boundary: canonical per-module measured dates are shown below. Session identifier, time of day, operator, printer/slicer profile and environmental conditions are Not recorded and are never inferred.

Measurement provenance

Canonical SQLite measured dates use ISO format; missing dates remain Not recorded.

Module	Measured date
Tensile	Not recorded
Impact	Not recorded
Stiffness	Not recorded

Status
Complete

Result modules
3/3

Specimen/result
records
41

Public details
Approved

Specimen and result quality

Module	Orientation	Average	Std. dev.	CV	Specimens	Confidence	Validation
Tensile	Upright	10,136 MPa	3,025 MPa	0,298%	10	10/10	OK
Tensile	Flat	43,912 MPa	2,008 MPa	0,046%	10	10/10	OK

Module	Orientation	Average	Std. dev.	CV	Specimens	Confidence	Validation
Impact	Upright	128,877 kJ/m ²	20,082 kJ/m ²	0,156%	10	10/10	OK
Impact	Flat	293,569 kJ/m ²	18,222 kJ/m ²	0,062%	10	10/10	OK
Stiffness	Three-point bend	3354,768 MPa	n/a	n/a	1	Complete	OK

Recorded native inputs

Module	Input set	Recorded values
Tensile	Upright force inputs (N)	47, 44, 90, 77, 80, 75, 31, 84, 73, 58
Tensile	Flat force inputs (N)	286, 300, 257, 291, 275, 289, 295, 284, 300, 278
Impact	Upright needle inputs (%)	5, 6,5, 7, 8,5, 8, 8,5, 8, 8, 8, 9
Impact	Flat needle inputs (%)	17,5, 16, 15, 18,5, 17, 18, 18,, 18, 17, 17,5
Stiffness	Revolutions / degrees	1 / 190

Approved test notes

Method and equipment context

Purpose-built tensile, pendulum impact and three-point bend apparatus are used with the governed Settings Manager constants consumed by ResultsService. Results are comparative and do not claim accredited-laboratory equipment.

[Testing methodology](#) · [Engineering methodology whitepaper](#) · [Download PDF](#)

reports/test-sessions/MAT0182/

